




Hygeia 4

Hands Free Sterile Area Telephone



- **Full key pad**
- **Flat membrane fascia, resists contamination**
- **Hands free operation (VOX)**
- **DTMF/LD dialling**
- **Audio-visual ring indication**
- **REN 1**
- **CE Compliant**
- **Flush or surface mounting**
- **Volume adjust on installation and on front panel**

The Hygeia is a fully electronic telephone that incorporates many features found on modern commercial telephones. It provides hands-free loudspeaking communication facilities, as intercoms PBX switching, or coupled direct to the public telecom network.

Hygeia is a flush or surface mounted unit incorporating a flat membrane operating panel. When installed with suitable interface sealants, a very high IP water resistant rating can be achieved.

The operating membrane is an impermeable multilayer chemically inert polyester.

Incoming calls are indicated by a flashing LED beacon and audible warble tone. To aid intelligibility, a volume control button is provided for noisy environments.

Call termination can either be through button depression, automatic time out or remote command.

Ringer operation is selectable either at installation or as remote programming.

Hygeia can be configured to be fully compatible with most PABX's or PTT networks. Loop disconnect (LD) and tone dialling (DTMF) systems are remotely selectable, as are recall systems, timed break recall (TBR) and earth loop recall (ELR).

Available as 18 button with 2 memory keys and volume (VOL) button.

GAI-Tronics Telephony

Hygeia 4

Hands Free Sterile Area Telephone

TECHNICAL SPECIFICATION

Speech:

Tested to the CTR21 specification.
Voice-switched (VOX) semi-duplex operation.
Additional half-duplex mode controlled remotely (optional local push-to-talk button)
Send & Receive levels remote programmable (1dB step)
Receive volume control button(s) adjusts level by +/- 6dB
Call timeout programmable from 1 to 42 minutes
Remote switch-off capability
Euro-wide network matching (factory set)

Dialling Data:

LD (pulse dialling) : 66:33, 10 ips, 800ms IDP
DTMF: 100ms to ITU-T Q23
Recall: TBR (Timed Break Recall), 100ms or ELR (Earth Loop Recall)

Other formats (factory set):

LD: 60:40, 10ips, 500ms / 800ms IDP
DTMF: 50ms
TBR: 300ms or 600ms

Full keypad with 2 memories, Recall and Volume button.

Safety: Tested to EN41003 and EN60950.

Ringing and Remote Maintenance:

Dual tone ringing through loudspeaker >75 dB @ 1m REN 1.
Auto-answer for remote programming: 0 to 15 rings.
Speech disabled during remote programming: call cleared down in favour of user dialling.

Sensing: Remote sensing of network loop current (2.5 mA resolution) and power-supply connection.

Power Supply: Regulated power supply required 9-12Vdc @ 500mA (included).

Memory Retention (autodiallers):

E² PROM - 10 year life.

Temperatures:

Operating: -20° C to +55° C
Storing: -40° C to +70° C

Relative Humidity: Up to 95% (non-condensing).

Weather Resistance: Up to IP65 dependent on installation.
Please call for advice on application.

Casing Material: Front face plate membrane is an impermeable multilayer chemically inert polyester.

Chemical Resistance: Resistant to: Alcohols, Dilute acids, Dilute alkalis, Esters, Hydrocarbons, Ketones, Household cleaning agents. (Tested to DIN 42 115).

Colour: White with blue printing

Weight: 1.1kg (3kg with backbox)

APPROVALS



This mark indicates compliance with the following directive;

R&TTE Directive 1999/5/EC




Optional Induction Loop for hearing impaired

This mark indicates compliance for inductively coupling to Hearing Aids having a 'T' switch position
Tested to ETS 300-381 and in accordance with ITU-T P37

For specific country approval, please call

DIMENSIONS



Overall (no back box): 352H X 181W X 48D mm

Fixing: 307H X 166W mm CRS

Cut out: 275H X 100W mm

ORDER CODE

Hygeia with stainless steel back box
028-02-1408-9B0

no back box
028-02-1408-900



GAI-Tronics, UK - Tel: +44 (0)1283 500500 - Fax: +44 (0)1283 500400 - www.gai-tronics.co.uk
GAI-Tronics Corporation, USA - Tel: +1(610) 777 1374 - Toll Free: 800 492 1212 - Fax: +1(610) 775 6540 - www.gai-tronics.com
GAI-Tronics S.r.l, Italy - Tel: +39 02 48601 460 - Fax: +39 02 4585 625
GAI-Tronics Corporation, Malaysia - Tel: +60 3 6277 6091 - Fax: +60 3 6277 6093
An ISO9001 Registered Company
The policy of GAI-Tronics is one of continuous improvement, therefore the company reserves the right to change specifications without notice.