



# Doro MemoryPlus 319i ph

## Amplified photo phone

MemoryPlus 319i ph is an excellent choice for people with reduced dexterity, hearing or memory. The ergonomic handset, large keypad and one-touch photo memory buttons are all specially designed to make MemoryPlus 319ph extremely easy to operate.

- ✓ Comfortable, ergonomically designed grip
- ✓ Easy to use – just lift and press
- ✓ Handset volume amplified by up to 35dB



# Doro MemoryPlus 319i ph

## Main features

Photokeys	4
-----------	---

## Memories

Redial memory	1
One touch memories	4

## Sounds & Signals

Monophonic ringtones:	3
Visual ring indicator	✓
Ringer volume settings except off	3
Ringer off setting	✓

## Acoustics

Receiving maximum level (dB RLR)	-35
Receiving maximum level (dB(A))	123
Receiving minimum level (dB(A))	88
Boost protection	✓
Tone adjustment at 250Hz (dB)	6
Tone adjustment at 4KHz (dB)	12
HAC (hearing aid compatible)	✓
HAC level sensitivity at 1KHz (dB-A/M)	-23
HAC frequency response permissible range	✓
HAC frequency response preferred range	✓
HAC linearity +/-1dB	✓
Maximum ringer volume (dB(A) at 1 meter)	91
Lowest ringer centre frequency (Hz)	700
Highest ringer centre frequency (Hz)	2000
Slide volume settings	✓

## Ergonomic sound™

Tone control	✓
--------------	---

## Ergonomics

Easy clean surfaces	✓
Easy grip comfortable handset	✓
Light weight handset (g)	220



# Doro MemoryPlus 319i ph

Easy to place handset



High contrast keys with low reflective finish



Concave keys



Low profile front for easy operation



## Technology

PSTN



*Doro shall not be held responsible for any errors or omissions contained herein. Specifications are subject to change without notice.*

